


ENTERO L SOFTENING LENS

28500 0150



 [View on website](#)



General info

LOCATION	indoor
WEIGHT (KG)	0.1

ENTERO L SOFTENING LENS

28500 0150

WHERE USED

28418 9210	ENTERO RD-L 92718
28418 9220	ENTERO RD-L 92730
28418 9230	ENTERO RD-L 92745
28418 9310	ENTERO RD-L 93018
28418 9320	ENTERO RD-L 93030
28418 9330	ENTERO RD-L 93045
28420 9010	ENTERO RD-L TW 96518
28420 9020	ENTERO RD-L TW 96530
28420 9030	ENTERO RD-L TW 96545
28435 9210	ENTERO RD-L TRIMLESS 92718
28435 9220	ENTERO RD-L TRIMLESS 92730
28435 9230	ENTERO RD-L TRIMLESS 92745
28435 9310	ENTERO RD-L TRIMLESS 93018
28435 9320	ENTERO RD-L TRIMLESS 93030
28435 9330	ENTERO RD-L TRIMLESS 93045
28437 9010	ENTERO RD-L TRIMLESS TW 96518
28437 9020	ENTERO RD-L TRIMLESS TW 96530
28437 9030	ENTERO RD-L TRIMLESS TW 96545
28447 9210	ENTERO RD-L X 92718
28447 9220	ENTERO RD-L X 92730
28447 9310	ENTERO RD-L X 93018
28447 9320	ENTERO RD-L X 93030
28449 9010	ENTERO RD-L X TW 96518
28449 9020	ENTERO RD-L X TW 96530
28518 9210	ENTERO SQ-L 92718
28518 9220	ENTERO SQ-L 92730
28518 9230	ENTERO SQ-L 92745
28518 9310	ENTERO SQ-L 93018
28518 9320	ENTERO SQ-L 93030
28518 9330	ENTERO SQ-L 93045
28520 9010	ENTERO SQ-L TW 96518
28520 9020	ENTERO SQ-L TW 96530
28520 9030	ENTERO SQ-L TW 96545
28535 9210	ENTERO SQ-L TRIMLESS 92718
28535 9220	ENTERO SQ-L TRIMLESS 92730
28535 9230	ENTERO SQ-L TRIMLESS 92745
28535 9310	ENTERO SQ-L TRIMLESS 93018
28535 9320	ENTERO SQ-L TRIMLESS 93030
28535 9330	ENTERO SQ-L TRIMLESS 93045
28537 9010	ENTERO SQ-L TRIMLESS TW 96518
28537 9020	ENTERO SQ-L TRIMLESS TW 96530
28537 9030	ENTERO SQ-L TRIMLESS TW 96545
28547 9210	ENTERO SQ-L X 92718
28547 9220	ENTERO SQ-L X 92730
28547 9310	ENTERO SQ-L X 93018
28547 9320	ENTERO SQ-L X 93030
28549 9010	ENTERO SQ-L X TW 96518
28549 9020	ENTERO SQ-L X TW 96530

Notes: