



## ENTERO SQ-M X TW 94018 B

28571 9010 B



AVAILABLE IN

**BLACK** 28571 9010 B

**FLEMISH BRONZE OUTDOOR** 28571 9010 FBRX

**ANTHRACITE (DARK GREY)** 28571 9010 N

**WHITE** 28571 9010 W



 [View on website](#)

### General info

<b>LOCATION</b>	outdoor
<b>INSTALLATION</b>	Ceiling Recessed
<b>CUTOUT SHAPE/SIZE (MM)</b>	square - 92 x 92
<b>RECESSED DEPTH (MM)</b>	140
<b>THICKNESS OF MOUNTING SURFACE (MM)</b>	12,5 or 25
<b>INGRESS PROTECTION</b>	IP65
<b>PROTECTION AGAINST MECHANICAL IMPACT</b>	IK06
<b>WEIGHT (KG)</b>	0.465
<b>ADJUSTABILITY</b>	0° to 20° swiveling, 355° rotatable
<b>INFORMATION</b>	REFLECTOR SP-18° EXCL.LED POWER SUPPLY 500mA-DC TW - (DALI DT8)

### Electrical info

<b>CLASS</b>	III
<b>DIM TYPE</b>	depending on type of external power supply
<b>ENERGY CLASS</b>	E
<b>CERTIFICATES</b>	CB, ENEC

### Lightsource info

<b>LIGHTSOURCE NAME</b>	LED
<b>LIGHTSOURCE</b>	LED array 9W / CRI>90 (R9: 50) / 1800K-4000K / 979lm
<b>TM-30 VALUES</b>	Rf: 89 / Rg: 100
<b>SDCM</b>	SDCM2
<b>RISKGROUP</b>	RG1
<b>LM80</b>	L90B10 > 50000
<b>LED TECHNICS (LIGHT SOURCE)</b>	979lm // 9W // 109lm/W
<b>LED TECHNICS (LUMINAIRE)</b>	596lm // 10W // 58lm/W

### Requirements

LED POWER SUPPLY 500mA-DC TW

# ENTERO SQ-M X TW 94018 B

28571 9010 B



## Accessories

---

- ENTERO M HONEYCOMB
- ENTERO M LINEAR SPREAD LENS
- ENTERO M SPREAD LENS
- ENTERO M SOFTENING LENS
- ENTERO M GLASS SBL

For detailed installation instructions, please consult the manual: [28571\\_XXX0\\_HAND.pdf](#)

## CEILING COMPATIBILITY

Ceiling Type	Mounting Kit
 System ceiling	-
 Plasterboard	-
 Stucanet	-
 Wood	-
 Stretched ceiling	-


# ENTERO SQ-M X TW 94018 B

28571 9010 B

## FINISH YOUR SPECIFICATION

### LED power supplies


#




**21012 0355** LED POWER SUPPLY 500mA-DC 2CH TW DIM5

1->2


### Light altering devices




**28500 0070** ENTERO M LINEAR SPREAD LENS




**28500 0080** ENTERO M SPREAD LENS



**28500 0090** ENTERO M SOFTENING LENS



**28500 0100** ENTERO M GLASS SBL



**28500 0110 B** ENTERO M HONEYCOMB SINGLE USE B

Notes: